



Siemens Low Voltage Circuit Protection Heavy Duty Safety Switches - Type ENCLOSED / SAFETY SWITCH Meets stds: UL. Built material: STEELdouble throw action. Rated 600V (60A) at 60Hz. Delivers 3WW3-Pole. Insulated. TYPE 1 enclosure with 2 or 3 point mounting. No special features listed.

General technical data	
mechanical service life (operating cycles) typical	10000
fastening method	SURFACE
number of poles	3
suitability for operation	LOAD TRANSFER BETWEEN POWER SOURCES
Electricity	
ampacity	60 A
supply voltage frequency rated value 50/60 Hz	Yes
Model	
product brand name	SIEMENS
product type designation	DOUBLE THROW SWITCH
type of electrical connection	MECHANICAL LUGS
Mechanical Design	
design of the housing	TYPE 3R/ 3S/ 12/ 13
design of the actuating element	DOUBLE THROW
material	STEEL
General product approval	
certificate of suitability	UL98

last modified:

9/16/2021 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

DTNF362J