

Siemens Low Voltage Circuit Protection General Duty Safety Switches. Type: ENCLOSED, SAFETY SWITCH Std: CSA V. Rating: 600V A. Rating: 200A Wattage: 3W No. Of Poles: 3P F. Rating: 60Hz Action: SINGLE THROW Material: STEEL Enclosure: TYPE 1. 2-3 point mounting holes. O. Cycles: 8000 O. Temperature: (-20F-120F) AMBIENT TEMPERATURE Environmental Conditions: INDOOR

General technical data	
principle of operation of the actuating element	SINGLE THROW
mechanical service life (operating cycles) typical	8000
number of poles	3
Electricity	
ampacity	200 A
Switching capacity	
switching capacity active power	3 W
Environmental conditions	
ambient temperature during operation maximum	49 °C
ambient temperature during operation minimum	-29 °C
Model	
product brand name	Siemens
product type designation	ENCLOSED/SAFETY SWITCH
Mechanical Design	
design of the housing	TYPE 1
material	STEEL
General product approval	
certificate of suitability	CSA

last modified:

9/15/2021 



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

GFC364