



Siemens Low Voltage Circuit Protection Heavy Duty Safety Switches. 600A 3P 600V 4W FUSED HD TYPE 3R

General technical data	
fastening method	SURFACE
number of poles	3
suitability for operation	DISCONNECTING MEAN FOR SERVICE ENTRANCE / LOADS
Electricity	
ampacity	600 A
Environmental conditions	
ambient temperature during operation maximum	85 °C
ambient temperature during operation minimum	-29 °C
Model	
product brand name	SIEMENS
product sub brand name	VBII
product type designation	HEAVY DUTY SWITCH
type of electrical connection	MECHANICAL LUGS
Mechanical Design	
design of the actuating element	SINGLE THROW
material	STEEL
General product approval	
certificate of suitability	UL98

last modified:

9/15/2021 



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[HF366NRA](#)