

Siemens Low Voltage Circuit Protection OEM Disconnect & Accessories. Type: OEM DISCONNECT SWITCH Std: UL A. Rating: 30-200A F. Rating: 60Hz Action: single throw Material: metal Enclosure: TYPE 3R/12 Mounting: PANEL MOUNTING Insulation: YES O. Cycles: 8000 O. Temperature: (-20F-120F) AMBIENT TEMPERATURE Environmental Conditions: INDUSTRIAL/OUTDOOR



General technical data	
fastening method	PANEL MOUNTING
Model	
product brand name	SIEMENS
product type designation	OEM DISCONNECT SWITCH
Mechanical Design	
material	METAL
General product approval	
certificate of suitability	UL
degree of protection NEMA rating	TYPE 3R/12

last modified: 12/21/2020 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[VBH112](#)