

Siemens Low Voltage Circuit Protection OEM Disconnect & Accessories. Type: OEM DISCONNECT SWITCH Std: UL A. Rating: 30-200A F. Rating: 60Hz Action: single throw Material: plastic Enclosure: TYPE 4X Mounting: FLANGE MOUNTING Insulation: YES O. Cycles: 8000 O. Temperature: (-20F-120F) AMBIENT TEMPERATURE Environmental Conditions: INDUSTRIAL CORROSIVE RESISTANT



General technical data	
fastening method	FLANGE MOUNTING
Model	
product brand name	SIEMENS
product type designation	OEM DISCONNECT SWITCH
Mechanical Design	
material	PLASTIC
General product approval	
certificate of suitability	UL
degree of protection NEMA rating	TYPE 4X

last modified:

1/6/2021 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

VBH14X