

Datasheet

USB DRIVE

3SE series

- High performance with USB 3.0 interface
- Low power consumption
- Wear-Leveling supported
- ECC engine coverage up to 60-bit/1024 Bytes
- Metal housing for robust usage
- 30μ golden finger for highly reliable data transfer quality



Introduction

The Innodisk USB Drive products provide high capacity USB flash memory storage that electrically complies with High-speed USB 3.0 interface & backward compatible with USB 2.0. The device features attractive small form factor and the connectivity over USB 3.0 and the NAND flash architecture provide a faster data transmission.


USB DRIVE

3SE series

Contact us for more information
about the USB DRIVE 3SE.

Innodisk is a service-driven provider of industrial embedded flash storage products and technologies, with a focus on the cloud computing, industrial/embedded, and aerospace and defense industries.

Diagram



Specifications

Headquarters (Taiwan)

5F., No.237, Sec. 1, Datong Rd.,
Xizhi Dist., New Taipei City 221,
Taiwan (R.O.C.)
Tel: +886-2-77033000
Email: sales@innodisk.com

Branch Offices:

USA
usasales@innodisk.com
+1-510-770-9421
Europe
eusales@innodisk.com
+31-(0)40-282-1818
Japan
jpsales@innodisk.com
+81-45-594-7581
China
sales_cn@innodisk.com
+86-755-21673689
www.innodisk.com

© 2021 Innodisk Corporation.
All right reserved. Specifications
are subject to change without
prior notice.

Interface	USB 3.0
Flash Type	SLC
Capacity	4GB~32GB
Max. Channels	1
Sequential R/W (MB/sec, max.)	100 / 85
Max. Power Consumption	0.70 W (5V x 140 mA)
Thermal Sensor	-
External DRAM buffer	-
H/W Write Protect	-
ATA Security	-
S.M.A.R.T.	-
Dimension (WxLxH)	16.5 X 48.3 X 7.6 mm
Environment	Vibration: 20G @ 7~2000Hz Shock: 1500G @ 0.5ms Storage Temperature: -40°C ~ +85°C MTBF: 3 million hours

20211005

Ordering Information

Operation Temp.	4GB	8GB	16GB	32GB
Standard Grade (0°C ~ +70°C)	DEUA1- 04GI61*C**SB	DEUA1- 08GI61*C**SB	DEUA1- 16GI61*C**SB	DEUA1- 32GI61SCASB
Industrial Grade (-40°C ~ +85°C)	DEUA1- 04GI61*W**SB	DEUA1- 08GI61*W**SB	DEUA1- 16GI61*W**SB	DEUA1- 32GI61SWASB

*, S/A = Flash mode

** . A = BGA / 1=TSOP

innodisk

www.innodisk.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Innodisk:

[DEUA1-04GI61SCASB](#) [DEUA1-04GI61SWASB](#) [DEUA1-08GI61SCASB](#) [DEUA1-08GI61SWASB](#) [DEUA1-16GI61SCASB](#) [DEUA1-16GI61SWASB](#) [DEUA1-32GI61SCASB](#) [DEUA1-32GI61SWASB](#)