

MIRO TR 24VDC FK OPTO-COUPLER MODULE

IN: 48 VDC - OUT: 48 VDC / 2 A

Art.No.: 6652501

Weight: 0.02



Country of origin: CZ

Model designation: MIRO,TR,24VDC,FK


Transistor 2 A

24 V DC

Spring clamp terminals

Link to Product**Illustration**

Product may differ from Image

**Header**

Material short text

MIRO,TR,24VDC,FK

Commercial data

URL Webshop

<https://shop.murrelektronik.com/6652501>

GTIN	4048879021876
ECLASS-6.0	27371601
ECLASS-6.1	27371604
ECLASS-7.0	27371604
ECLASS-7.1	27371604
ECLASS-8.0	27371604
ECLASS-8.1	27371604
ECLASS-9.0	27371604
ECLASS-9.1	27371604
ECLASS-10.0.1	27371604
ECLASS-10.1	27371604
ECLASS-11.0	27371604
ECLASS-11.1	27371604
ECLASS-12.0	27371604
ECLASS-13.0	27371604
ECLASS-14.0	27371604
ETIM-5.0	EC001504
ETIM-6.0	EC001504
ETIM-7.0	EC001504
ETIM-8.0	EC001504
customs tariff number	85414900
EAN	4048879021876
Packaging unit	1
Electrical data Input	
Input voltage DC min.	10 V
Input voltage DC max.	48 V
Input voltage OFF DC min.	0 V
Input voltage OFF DC max.	5 V
Current input DC	7 mA
Electrical data Output	
Voltage drop DC max.	0.3 V
Quiescent current OFF max.	0.01 mA
Switch on delay max.	1 ms
Switch off delay max.	5 ms
Voltage switching DC min.	5 V
Switching voltage DC max.	48 V
Switching current min.	1 mA
Switching current max.	2 A
Switching frequency ohmic max.	10 Hz
Switching frequency inductive max.	1 Hz
Diagnostics	
Status indication LED	yellow
Device protection Electrical	
Rated surge voltage	25 kV
Device protection Media	
Flame resistance	flame retardant
Mechanical data Material data	
Material housing	Plastic
Color housing	black
Mechanical data Mounting data	
Height	78 mm

Width	62 mm
Depth	70 mm
Mounting method	geschnappt
Suitable for mounting type	(EN 60715), mounting rail

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	60 °C

Connection type 4

Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	13 +
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	14
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	A 1
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	A 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Murrelektronik:](#)

[6652501](#)