



Series Part Numbers

Connector Code -XX-	Description	P / N
AM	SMA Plug	S765FL-L-AM-915
AH	SMA Plug Reverse Polarity	S765FL-L-AH-915
MM	MMCX Straight Plug	S765FL-L-MM-915
RMM	MMCX Right Angle Plug	S765FL-L-RMM-915

Electrical Properties:

Frequency Range: 902~928 MHz
 Impedance: 50Ω nominal
 VSWR: <2.0:1
 Gain: 2 dBi
 Radiation: Omni
 Polarization: Vertical

Mechanical Properties:

Cable: Low loss cable J100
 Cable Length: L to be defined in inches
 Connector: XX to be specified by customer
 Material:
 Body: ABS+PC (Black)
 Base: Brass with Nickel plating
 Operation Temp.: -20°C to +65°C
 Storage Temp.: -30°C to +75°C

This is a RoHS compliant product.

TITLE	900 MHz External Antenna 765 Model		Rev. Date	SHEET
			01/03/11	1 OF 1
UNIT	DWG. NO.	S765FL-L-XX-915		
mm(In.)				
SCALE				
none				

NEARSON

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Banner Engineering:](#)

[BWA-902-D](#)