

Detailed Specifications

Frame Width:	200[mm]
Frame Height:	200[mm]
Frame Depth:	51[mm]
Max. Air Flow:	590[CFM]
Max. Air Flow:	16.71[m3 per min]
Max. Static Pressure:	3.324[In H2O]
Max. Static Pressure:	828[Pa]
Fan Speed:	5000[RPM]
Noise:	67[dB]
Life Expectancy:	40 degree C 70,000 Hours[L10]
Bearing Type:	Ball Bearing
Speed Control:	PWM
Nominal Voltage:	48[V]
Operating Voltage - Lower:	30[V]
Operating Voltage - Upper:	72[V]
Current:	1.3[A]
Input Power:	62.4[W]
Mass:	1200[g]
IP Rating:	Non IP model
Tach / Locked Rotor Output:	Tach Output
Status:	Active

PWM Speed Control Fans

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[R200A1-051-D0750](#)