





A	6	Pin 1	H62	Gold	1	DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED TOLERANCES ANGLES = ±5° UP TO 6 = ±0.2 6-40 = ±0.4 40-120 = ±0.6 120-315 = ±1 ABOVE 315 = ±1.6 THIRD_ANGLE SCALE 1.5/1	APPROVED CHECKED DRAWN	DATE DATE DATE	Io Audio Technologies Description EV Series 3 Pin Female XLR Chassis Connector			
	5	Pin 2	H62	Gold	1							
	4	Pin 3	H62	Gold	1							
	3	Ground Terminal	H62	Nickel	1							
	2	Contact Housing	PA	Black	1							
	1	Latch Release	H62	Nickel	1				PART NO. IO-XLR3-F-EV		REV.	A1
	NO.	DESCRIPTION	MATERIAL	FINISH	Q'TY							

F
E
D
C
B
A



1 2 3 4 5 6 7 8

F
E
D
C
B
A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Io Audio:](#)

[IO-XLR3-F-EV](#) [IO-XLR3-M-EV](#)