

# OA600ST Series

## 432x338x44.5mm

(17"x 13.3"x 1.75")



# OA300ST Series

## 432x203x44.5mm

(17"x 8"x 1.75")



Lighted rocker switch

Resettable circuit breaker.

Unit mounts in to any standard 19" rack.

Tray features 6 high performance sealed ball bearing fans.

Black wrinkle finish.

Operating temperature: -40 to +75 degrees C



Lighted rocker switch

Resettable circuit breaker.

Unit slides in to any standard 19" rack.

Tray features 3 high performance sealed ball bearing fans.

Black wrinkle finish.

Operating temperature: -40 to +75 degrees C

Part Number	OAT600ST	OAT602ST	OAT300ST	OAT302ST
No. of Fans	6	6	3	3
Bearing System	Dual Ball Bearing	Dual Ball Bearing	Dual Ball Bearing	Dual Ball Bearing
Nominal Voltage (60Hz)	115 VAC	230 VAC	115 VAC	230 VAC
Input Power	90 Watts	90 Watts	45 Watts	45 Watts
Rated Speed (RPM)	3000	3000	3000	3000
Airflow (CFM)	620	620	310	310
Noise Level (dB)	56	56	53	53
Life Expectancy	60,000 Hrs (25C)	60,000 Hrs (25C)	60,000 Hrs (25C)	60,000 Hrs (25C)
Connection	2M Modular Power Cord	2M Modular Power Cord	2M Modular Power Cord	2M Modular Power Cord

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Orion Fans:

[OA600ST-230](#) [OA600ST-120](#) [OAT300ST](#) [OAT302ST](#) [OAT600ST](#) [OAT602ST](#) [OAT300ST-03](#) [OAT302ST-03](#)