

10 Series

Electromechanical Totalizer



A 6 figure general purpose, rugged, electromechanical counter, either panel or base mounted, with manual knob reset, key reset, or thumb wheel reset. Frame and housing provides rigid support for accurate alignment and trouble-free use. Distinctive numerals enhance visibility under adverse viewing conditions.

Key Features

- Panel or base mount
- Rigid support for accurate alignment
- Enhanced visibility
- Manual knob, key or thumb wheel reset
- Options for:
 - Lead lengths
 - Terminations
 - Mounting
 - 1071-024S - additional key for model 1026

Applications


- Molding Machines
- Punch Press
- Printing presses
- Test Labs
- Secondary Machines

Common Specifications


Figures	6 figures, white on black, 0.19" [5mm] high
Reset	Knob, lock and key, or thumb wheel
Speed	1,000 counts/minute (min. 30ms - on, 30ms - off)
Voltage	115VAC (+/- 10%, but not to exceed 10 volts)
Power	7.8 watts (nominal)
Mounting	Base or panel
Terminations	(2)#22 AWG 105°C wire leads, 8" [203mm] long
Operating Life	> 5,000,000
Temp. Range	-15°F to +140°F [-26°C to +60°C]
Approvals	UL Recognized, CE Compliant, ROHS
Weight	18 to 22 oz. [510 to 624g]




Dimensions



Mounting holes: 0.15" [3.8mm] Dia.



Screws provided: 6-32 x 0.6 [15.2mm]
 Panel cutout: 3.85" x 1.75" [97.8 x 44.5mm]



Screws provided: 6-32 x 0.6 [15.2mm]
 Panel cutout: 4.88" x 1.75" [124.0 x 44.5mm]

Part Numbers:

2-1006	115VAC, base mount, knob reset
P2-1006	115VAC, panel mount, thumb wheel reset
P32-1026	115VAC, panel mount, lock and key reset



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Trumeter:

[1071-024S](#) [2-1006](#) [P2-1006](#) [P32-1026](#)