

18 Series

Electronic Hand Tally Counter



The 18 Series electronic hand tally counter are available with a choice of Add only or Add/Subtract models. Counts are input using large positive action buttons. The Add model has a single count button and the Add/Subtract model has two separate count buttons. The counter is manufactured from impact-resistant plastic, combining lightweight with outstanding durability.

Key Features

- Add or Add/Subtract models
- Beep at every count with the option of switching the sound off for silent operation
- Long life battery (replaceable) - typical 250 days on silent
- Large LCD display
- No mechanical parts to wear out
- Large rubber buttons for comfort of use
- Ergonomically designed for ease of use
- Carrying cord - 9.0" [229mm]
- Light weight

Applications

- Inventory
- Traffic
- Attendance
- Food Portions
- Blood Cells

Specifications

Display	4 digit LCD 0.35" [9mm] high
Battery Operating Life	250 days (without sound)
Reset	Push button
Operating Temperature	+32°F to +122°F [0°C to +50°C]
Weight	0.7 oz (20g)
Color	Black case with blue buttons (Add Only) or green and red buttons (Add/Subtract)
Dimensions:	2.4" L x 1.4" W x 0.6" D [60mm x 35mm x 15mm]

Operating Instructions

- Press On/Off/Reset button to power ON the unit
- Add model - Press count button to increment count
- Add/Subtract model - Press the "+" button to Add, Press the "-" button to Subtract
- To reset counter press the On/Off/Reset button for 3 seconds
- To switch the sound Off/On at any time, hold the count button down for 3 seconds
- To turn Off, press the On/Off/Reset for 3 seconds when counter display is at "0"

Battery Replacement

- When the display gets dim, replace the battery.
- Use 1 type AG10 1.5 V or equivalent
- Observe polarity (\pm) during replacement

Part Numbers

E2M-1804	Electronic Hand Tally (Add only)
E3-1804	Electronic Hand Tally (Add/Subtract)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Trumeter:

[E2M-1804](#) [E3-1804](#)