

# 2300, 2401 & 2701 Series

## Mechanical Length Measuring Unit



**Heavy duty measuring unit, dual measuring wheels for better stability and contact, frame/bulkhead mounted.**

These rugged instruments have a wide range of applications where an accurate record of length is required. They are strong, heavy duty units for use on calendars, tenters, rolling, ribbon winding, textile machinery and almost all other continuous manufacturing processes. The 2701 (twin wheel) and the 2401 (single wheel) units are mounted or hung from a supplied stay rod, 17.99" (457mm). The 2300 bolts directly onto a bulkhead or frame member. All other models incorporate a hinge arrangement on the stayrod so they can be positioned at any angle. Incorporates the 3602 counter and measuring wheels.


### Key Features

- Uses standard measuring wheels
- Can be tilted out of the way when not in use
- The 2300 bolts directly onto a bulkhead or frame member
- The integral hinge arrangement allows the unit to be positioned at any angle
- The measuring wheels supplied can be 0.5m or 0.3m (18in or 12in) circumference (specify when ordering)
- The weight of the assembly holds it in contact with the material being measured

### Specification

<b>Display</b>	6 digit 0.25" (6.4mm)
<b>Measurement Options</b>	Imperial or metric
<b>Max speed of travel</b>	3,000 RPM Mechanical
<b>Accuracy</b>	+/- 1%
<b>Shaft Diameter</b>	7mm
<b>Units of Measurement</b>	Metres/centimeters, yards/eighths or feet/inches (other measurements may be available to special order)
<b>Packed Dimensions</b>	<b>2300:</b> 180mm (7.09in) x 200mm (7.87in) x 270mm (10.63in) <b>2401/2701:</b> 500mm (19.69in) x 250mm (9.81in) x 100mm (3.94in)
<b>Nett Weight</b>	<b>2300:</b> 2.81lb (1.3kg) <b>2401:</b> 3.74lb (1.7kg) <b>2701:</b> 4.4lb (2.0kg)

# 2300 / 2401 / 2701 Subassemblies



## Part Numbers


<b>A</b>	007628-02	<b>STAYROD</b> 460mm (18") long, 14mm Ø
<b>B</b>	001647-01	<b>STAND</b> (2401, 2701) for use with stayrod
<b>C</b>	001667-01	<b>COUNTER BRACKET</b> (2401, 2701) for use with stayrod
<b>D</b>	005697-01	<b>COUNTER BRACKET AND HINGE</b> (2300)
<b>E</b>	007628-03	<b>LUG</b>

## OTHER PARTS


005697-03	<b>COMPLETE MOUNTING ARRANGEMENT</b> (2401, 2701)
016390-01	<b>WHEEL FIXING BUSHING KIT</b> 3 sizes
001921-36	<b>7mm TONGUE BUSHING</b>
019281-02	<b>3602 RESET KIT</b> (handle, shaft, springs)
020655-01	<b>RESET HANDLE</b>

## Dimensions

Product Dimensions 2300



Product Dimensions 2401 | 2701



## Length Measuring Ordering Information

To order a 2300, 2401 or 2701:

1. Select from the three different basic units,
2. Select the wheel surface type
3. Select the wheel circumference from option
4. Select the unit of measurement
5. Select the direction of travel

### 1. Select one of the units available from below

- 2300** Measuring counter with hinged bracket and two wheels
- 2401** Measuring counter with stand, stay rod, counter mounting bracket and one wheel
- 2701** Measuring counter with stand, stay rod, counter mounting bracket and two wheels

### 2. Select one of the measuring wheels listed below

- 1** Rubber covered plastic wheel(s)
- 5** Knurled aluminium wheel(s)\*
- \*(only available in 12" and 18" sizes)

### 3. Select the circumference for the wheel(s)


- 1** 1/2 metre wheel(s)
- 2** 1/3 metre wheel(s)
- 3** 18 inch wheel(s)
- 4** 12 inch wheel(s)

### 4. Select reading

- MY** Yards & 1/8ths
- MFY** Full Yards
- MF** Feet & Inches
- MFF** Full Feet
- MC** Metres & Centimeters
- MFM** Full Metres

### 5. Select direction of travel

- C** Top coming
- G** Top going



### Example of full order code

2701 Unit (stand, stayrod and 2 wheels) with 18" rubber covered plastic wheels, reading yards & 1/8ths, direction top going.

The full order code is: **2701-13MYG**

## Measuring Wheel Ordering Information

Material	Width	12" circumference	18" circumference	1/3m circumference	1/2m circumference
Rubber Covered Plastic	3/4" (19mm)	007571	007573	007905	007574
Knurled Aluminum	3/4" (19mm)	001558	001622		



### Trumeter (Europe)

Pilot Mill  
Alfred Street  
Bury,  
BL9 9EF  
Tel: +44 161 674 0960  
Email: sales.uk@trumeter.com

### Trumeter (The Americas)

6601 Lyons Rd, Suite H-7,  
Coconut Creek, Florida  
FL 33073,  
USA  
Tel: +1 954 725 6699  
Email: sales.usa@trumeter.com

### Innovative Design Technologies Sdn. Bhd

Lot 5881, Lorong Iks Bukit Minyak 1  
Taman Perindustrian Iks, 14000 Bukit Tengah  
Penang, Malaysia  
Web: www.idtworld.com  
Tel: + 604 5015700  
Email: sales.my@idtworld.com

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Trumeter:](#)

[001647-01](#) [001667-01](#) [005697-01](#) [005697-03](#) [007628-02](#) [007628-03](#) [2300-11MCC](#) [2300-11MCG](#) [2300-11MFMG](#)  
[2300-12MCC](#) [2300-12MCG](#) [2300-12MFMC](#) [2300-12MFMG](#) [2300-13MFFC](#) [2300-13MFFG](#) [2300-13MFYG](#) [2300-](#)  
[13MYC](#) [2300-13MYG](#) [2300-14MFC](#) [2300-14MFFC](#) [2300-14MFFG](#) [2300-14MFG](#) [2300-14MFYC](#) [2300-14MFYG](#)  
[2300-14MYC](#) [2300-14MYG](#) [2300-53MFC](#) [2300-53MFFC](#) [2300-53MFFG](#) [2300-53MFG](#) [2300-53MFYG](#) [2300-53MYC](#)  
[2300-53MYG](#) [2300-54MFFC](#) [2300-54MFFG](#) [2300-54MFG](#) [2300-54MFYC](#) [2300-54MYC](#) [2300-54MYG](#) [2401-](#)  
[11MCC](#) [2401-11MCG](#) [2401-11MFMC](#) [2401-11MFMG](#) [2401-12MCC](#) [2401-12MCG](#) [2401-12MFMC](#) [2401-12MFMG](#)  
[2401-13MFC](#) [2401-13MFFC](#) [2401-13MFFG](#) [2401-13MFG](#) [2401-13MFYC](#) [2401-13MFYG](#) [2401-13MYC](#) [2401-](#)  
[13MYG](#) [2401-14MFC](#) [2401-14MFFC](#) [2401-14MFFG](#) [2401-14MFG](#) [2401-14MFYC](#) [2401-14MFYG](#) [2401-14MYC](#)  
[2401-14MYG](#) [2401-53MFFC](#) [2401-53MFFG](#) [2401-53MFYC](#) [2401-54MFC](#) [2401-54MFFC](#) [2401-54MFFG](#) [2401-](#)  
[54MFG](#) [2401-54MFYC](#) [2401-54MFYG](#) [2401-54MYG](#) [2701-11MCC](#) [2701-11MCG](#) [2701-11MFMC](#) [2701-11MFMG](#)  
[2701-12MCC](#) [2701-12MCG](#) [2701-12MFMC](#) [2701-12MFMG](#) [2701-13MFC](#) [2701-13MFFC](#) [2701-13MFFG](#) [2701-](#)  
[13MFG](#) [2701-13MFYC](#) [2701-13MFYG](#) [2701-13MYC](#) [2701-13MYG](#) [2701-14MFC](#) [2701-14MFFC](#) [2701-14MFFG](#)  
[2701-14MFG](#) [2701-14MFYC](#) [2701-14MFYG](#) [2701-14MYC](#) [2701-14MYG](#) [2701-53MFFC](#) [2701-53MFFG](#) [2701-](#)  
[53MFYC](#)