

Switches Power Switches

5A 250V AC Qualified Primary Input Voltage Selection Type SDKP Series

Part number **SDKPA40300**

! Not Recommended for New Designs ?



? Reference Drawings

? Inquiry

Print

Type	Slide		
Circuit arrangement	DPDT		
Travel	6.0mm		
Operating force	10± +10 -5 N		
Mounting method	Self-tap (for M3)		
Terminal type	Right angle		
Dimensions (W×D×H)	42.0×15.6×14.0mm		
C-UL-US	5A 250V AC		
SEMKO	5A 250V~		
Ratings satisfying local electrical appliance and material safety law	250V 5Aキ		
Operating temperature range	-10℃ to +60℃		
Rating	5RA 250V AC		
Electrical performance	Contact resistance	100mΩ max.	
	Insulation resistance	500MΩ min. 500V DC	
	Voltage proof	2000V AC for 1 minute	
Mechanical performance	Terminal strength	10N for 1minute	
	Actuator strength	Operating direction	50N
		Perpendicular direction	50N
Durability	Operating life	100 cycles Without load	
Environmental performance	Cold	-20℃ 96h	
	Dry heat	85℃ 96h	
	Damp heat	40℃, 90 to 95%RH 96h	
Minimum order unit(pcs.)	Japan	100	
	Export	1,000	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Alps Alpine:](#)

[SDKPA40300](#)