

Potentiometers Slide Potentiometer (Master type)
Low-profile Master Type (Slim Type) RS**N11S Series

Part number

RS60N11S4006

! Not Recommended for New Designs ?



Reference Drawings



Inquiry



Print

Number of resistor elements		Single-unit
Direction of lever		Vertical
Travel		60mm
Lever type		4
Length of lever		20mm
Total resistance		10k Ω
Resistance taper		1B
Terminal style		For PC board
Operating temperature range		-10°C to +60°C
Durability	Operating life	30,000 cycles
Electrical performance	Total resistance tolerance	$\pm 20\%$
	Maximum operating voltage	200V AC, 10V DC
	Rated power	0.2W
	Insulation resistance	100M Ω min. 250V DC
	Voltage proof	250V AC for 1 minute
Mechanical performance	Operating force	0.3(+0.5, -0.25)N
	Stopper strength	100N
	Lever push-pull strength	50N
	Lever wobble (Both side)	3.2mm
	Lever deviation (One side)	0.5mm max.
Minimum order unit(pcs.)	Japan	600
	Export	1200

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Alps Alpine:](#)

[RS60N11S4006](#)