


For Tap Thru and Blind Tap information see chart

Tapped Thru up to and including these lengths			Longer Lengths
Thread	Aluminum, Brass, Steel & Nylon	Stainless Steel	Tap Each End
0-80	.375	.250	.187
2-56	.750	.625	.187
4-40	1.00	.750	.250
6-32	1.00	1.00	.375
8-32	1.00	1.00	.437
10-32	1.125	1.00	.500
12-24	1.125	1.00	.500
25-20	1.250	1.250	.625

All base materials are RoHS compliant

Drawing not to scale	Title: Hex Female Standoff
Break all sharp edges on outside diameters	Part Number: FC2056-440-SS
All base materials are RoHS compliant	Material: Stainless Steel
Tolerances (Unless Specified) <u>Decimal</u> .XXX ± .005 .XX ± .010  <u>Fraction</u> ± .005  <u>Angle</u> ± 3°  <u>Millimeters</u> ± .13  <u>Nylon</u> ± .010  <u>Metric Nylon</u> ± .25	Finish: Plain
	  1235 Tradeport Drive, Orlando, FL 32824 Tel: 407-226-2112 Fax: 407-226-3370 www.Fascomp.com

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Fascomp:](#)

[FC2056-440-SS](#)