


For Tap Thru and Blind Tap information see chart

| Tapped Thru up to and including these lengths | | | Longer Lengths |
|---|--------------------------------|-----------------|----------------|
| Thread | Aluminum, Brass, Steel & Nylon | Stainless Steel | Tap Each End |
| 0-80 | .375 | .250 | .187 |
| 2-56 | .750 | .625 | .187 |
| 4-40 | 1.00 | .750 | .250 |
| 6-32 | 1.00 | 1.00 | .375 |
| 8-32 | 1.00 | 1.00 | .437 |
| 10-32 | 1.125 | 1.00 | .500 |
| 12-24 | 1.125 | 1.00 | .500 |
| 25-20 | 1.250 | 1.250 | .625 |

All base materials are RoHS compliant

| | |
|---|--|
| Drawing not to scale | Title: Hex Female Standoff |
| Break all sharp edges on outside diameters | Part Number: FC2100-832-B-5 |
| All base materials are RoHS compliant | Material: Brass |
| Tolerances (Unless Specified) <u>Decimal</u> .XXX \pm .005 .XX \pm .010 <u>Fraction</u> \pm .005 <u>Angle</u> \pm 3° <u>Millimeters</u> \pm .13 <u>Nylon</u> \pm .010 <u>Metric Nylon</u> \pm .25 | Finish: Nickel Plate |
| |  1235 Tradeport Drive, Orlando, FL 32824 Tel: 407-226-2112 Fax: 407-226-3370 www.Fascomp.com |
| | |
| | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Fascomp:](#)

[FC2100-832-B-5](#)