



*Short lengths tapped to maximum depth

| *Short Lengths Minimum Internal Thread Depth | | | | | | | | | |
|--|------|------|------|------|------|------|------|------|------|
| Body Lengths in Decimal | | | | | | | | | |
| Thread | .187 | .250 | .312 | .375 | .437 | .500 | .562 | .625 | .750 |
| 2-56 | .095 | .150 | | | | | | | |
| 4-40 | .100 | .150 | .200 | | | | | | |
| 6-32 | .090 | .130 | .190 | .250 | .300 | | | | |
| 8-32 | .090 | .130 | .190 | .250 | .300 | .355 | | | |
| 10-32 | .090 | .125 | .190 | .250 | .300 | .355 | .434 | .475 | |
| 12-24 | .070 | .110 | .160 | .195 | .250 | .335 | .424 | .465 | |
| 25-20 | .060 | .090 | .135 | .160 | .250 | .310 | .365 | .430 | .553 |
| 31-18 | .060 | .080 | .125 | .150 | .220 | .280 | .335 | .400 | .475 |

All base materials are RoHS compliant

| | |
|---|---|
| Drawing not to scale | Title: Hex Male-Female Standoff |
| Break all sharp edges on outside diameters | Part Number: FC4463-256-A |
| All base materials are RoHS compliant | Material: Aluminum |
| Tolerances (Unless Specified) <u>Decimal</u> .XXX ± .005 .XX ± .010 <u>Fraction</u> ± .005 <u>Angle</u> ± 3° <u>Millimeters</u> ± .13 <u>Nylon</u> ± .010 <u>Metric Nylon</u> ± .25 | Finish: Plain |
| | |
| | |
| | |
| | 1235 Tradeport Drive, Orlando, FL 32824 Tel: 407-226-2112 Fax: 407-226-3370 www.Fascomp.com |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Fascomp:](#)

[FC4463-256-A](#)