



\*Short lengths tapped to maximum depth

*Short Lengths Minimum Internal Thread Depth									
Body Lengths in Decimal									
Thread	.187	.250	.312	.375	.437	.500	.562	.625	.750
<b>2-56</b>	.095	.150							
<b>4-40</b>	.100	.150	.200						
<b>6-32</b>	.090	.130	.190	.250	.300				
<b>8-32</b>	.090	.130	.190	.250	.300	.355			
<b>10-32</b>	.090	.125	.190	.250	.300	.355	.434	.475	
<b>12-24</b>	.070	.110	.160	.195	.250	.335	.424	.465	
<b>25-20</b>	.060	.090	.135	.160	.250	.310	.365	.430	.553
<b>31-18</b>	.060	.080	.125	.150	.220	.280	.335	.400	.475

All base materials are RoHS compliant

Drawing not to scale	Title: Hex Male-Female Standoff
Break all sharp edges on outside diameters	Part Number: FC4537-440-SS
All base materials are RoHS compliant	Material: Stainless Steel
Tolerances (Unless Specified) <u>Decimal</u> .XXX ± .005 .XX ± .010  <u>Fraction</u> ± .005  <u>Angle</u> ± 3°  <u>Millimeters</u> ± .13  <u>Nylon</u> ± .010  <u>Metric Nylon</u> ± .25	Finish: Plain  <i>"The Good Guys"</i> 
	1235 Tradeport Drive, Orlando, FL 32824 Tel: 407-226-2112 Fax: 407-226-3370 <a href="http://www.Fascomp.com">www.Fascomp.com</a>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Fascomp:](#)

[FC4537-440-SS](#)