


*Short lengths tapped to maximum depth

*Short Lengths Minimum Internal Thread Depth									
Body Lengths in Decimal									
Thread	.187	.250	.312	.375	.437	.500	.562	.625	.750
2-56	.095	.150							
4-40	.100	.150	.200						
6-32	.090	.130	.190	.250	.300				
8-32	.090	.130	.190	.250	.300	.355			
10-32	.090	.125	.190	.250	.300	.355	.434	.475	
12-24	.070	.110	.160	.195	.250	.335	.424	.465	
25-20	.060	.090	.135	.160	.250	.310	.365	.430	.553
31-18	.060	.080	.125	.150	.220	.280	.335	.400	.475

All base materials are RoHS compliant

Drawing not to scale	Title: Hex Male-Female Standoff
Break all sharp edges on outside diameters	Part Number: FC4574-1032-A
All base materials are RoHS compliant	Material: Aluminum
Tolerances (Unless Specified) <u>Decimal</u> .XXX ± .005 .XX ± .010 <u>Fraction</u> ± .005 <u>Angle</u> ± 3° <u>Millimeters</u> ± .13 <u>Nylon</u> ± .010 <u>Metric Nylon</u> ± .25	Finish: Plain
	 1235 Tradeport Drive, Orlando, FL 32824 Tel: 407-226-2112 Fax: 407-226-3370 www.Fascomp.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Fascomp:](#)

[FC4574-1032-A](#)