


Captive Screw Type 2 8-32 Thread



Create a part number:

Length	Material	Finish
FCXXXX	XX	XX

Captive Screws - 8-32 Thread				
✓ FCXXXX	Length (L)	S.L. +.010 -.010	D. +.010 -.000	
FC0403	7/16	1/8	.078	
FC0404	1/2	3/16	.078	
FC0405	9/16	1/4	.078	
FC0406	5/8	5/16	.078	
FC0407	11/16	3/8	.078	
FC0408	3/4	7/16	.078	
FC0409	13/16	1/2	.078	
FC0410	7/8	9/16	.078	
FC0411	15/16	5/8	.078	
FC0412	1	11/16	.078	
FC0413	1-1/16	3/4	.078	
FC0414	1-1/8	13/16	.078	
FC0415	1-3/16	7/8	.078	
FC0416	1-1/4	15/16	.078	

Material		
✓	Material Code (XX)	
	B	Brass
	S	Steel
	SS	Stainless Steel

✓	Compatible Finish (XX)	
	B, S, SS	0 - Plain
	B, S	5 - Nickel Plate (QQ-N-290)
	B, S	12 - Zinc Clear (ASTM-B-633)
	B, S	16 - Electro Tin (MIL-T-10727 TYPE 1)
	SS	20 - Passivation (MIL-F-14072D)
	B, S, SS	26 - Black Oxide
	B, S	28 - Zinc Yellow (ASTM-B-633)

Tolerances
Unless otherwise Specified
 .xxx +/- .005
 .xx +/- .010
 Angular +/- 1 Degree
 Linear +/- .005
Break all sharp edges



Source Control Drawing:
 To be produced by
 Fascomp Electronic Hardware

This document is the property of Fascomp Inc. and shall not be reproduced, distributed, or used as a basis for manufacturing without written permission from Fascomp Inc.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Fascomp:

[FC0403-SS](#) [FC0404-SS](#) [FC0405-SS](#) [FC0406-SS](#) [FC0407-SS](#) [FC0408-SS](#) [FC0409-SS](#) [FC0410-SS](#) [FC0411-SS](#)
[FC0412-SS](#)