


1/8 Round Internal Thread Handles



✓	FCXXXX	Length (L) +/- .031	Leg Height (H) +/- .031
	FC8000	3/4	1/2
	FC8001	13/16	1/2
	FC8002	7/8	1/2
	FC8003	1	1/2
	FC8004	1-1/4	1/2
	FC8005	1-1/2	1/2
	FC8006	2	1/2
	FC8007	3/4	3/4
	FC8008	13/16	3/4
	FC8009	7/8	3/4
	FC8010	1	3/4
	FC8011	1-1/4	3/4
	FC8012	1-1/2	3/4
	FC8013	2	3/4
	FC8014	1	1
	FC8015	1-1/4	1
	FC8016	1-1/2	1
	FC8017	1-3/4	1
	FC8018	2	1
	FC8019	1	1-1/4
	FC8020	1-1/4	1-1/4
	FC8021	1-1/2	1-1/4
	FC8022	1-3/4	1-1/4
	FC8023	2	1-1/4
	FC8024	1	1-1/2
	FC8025	1-1/4	1-1/2
	FC8026	1-1/2	1-1/2
	FC8027	1-3/4	1-1/2
	FC8028	2	1-1/2
	FC8029	1-1/4	2
	FC8030	1-1/2	2
	FC8031	1-3/4	2
	FC8032	2	2
	FC8033	2-1/2	2
	FC8034	3	2

Create a part number:

Part	Thread	Material	Finish
FCXXXX	XXX	XX	XX

Thread (A)			
Short lengths, 'A' tapped to maximum depth			
	Code (XXX)	Thread	(A)
✓	256	2-56	3/16

Material		
✓	Material Code (XX)	
	A	Aluminum
	B	Brass
	SS	Stainless Steel

✓	Compatible Finish	
	A, B, S, SS	0 - Plain
	B, S	5 - Nickel Plate (QQ-N-290)
	A	6 - Iridite #14 Gold (MIL-C-5541E)
	A	7 - Iridite Clear (MIL-C-5541E)
	A	9 - Alodine 1200
	B, S	12 - Zinc Clear (ASTM-B-633)
	B, S	16 - Electro Tin (MIL-T-10727 TYPE 1)
	SS	20 - Passivation (MIL-F-14072D)
	A	22 - Clear Anodize (MIL-A-8625-TYPE2) (Sulphuric) Hot Water Seal (Clear)
	A	24 - Black Anodize (MIL-A-8625)
	B, S, SS	26 - Black Oxide
	B, S	28 - Zinc Yellow (ASTM-B-633)

Source Control Drawing:
To be produced by
Fascomp Electronic Hardware

Tolerances
Unless otherwise Specified
.xxx +/- .005
.xx +/- .010
Angular +/- 1 Degree
Linear +/- .005
Break all sharp edges



This document is the property of
Fascomp Inc. and shall not be
reproduced, distributed or used as a
basis for manufacturing without
written permission from Fascomp
Inc.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Fascomp:

[FC8000-256-A](#) [FC8000-256-A-24](#) [FC8000-256-SS](#) [FC8001-256-A](#) [FC8001-256-A-24](#) [FC8001-256-SS](#) [FC8002-256-A](#) [FC8002-256-A-24](#) [FC8002-256-SS](#) [FC8003-256-A](#) [FC8003-256-A-24](#) [FC8003-256-SS](#) [FC8004-256-A](#) [FC8004-256-A-24](#) [FC8004-256-SS](#) [FC8005-256-A](#) [FC8005-256-A-24](#) [FC8005-256-SS](#) [FC8006-256-A](#) [FC8006-256-A-24](#) [FC8006-256-SS](#) [FC8007-256-A](#) [FC8007-256-A-24](#) [FC8007-256-SS](#) [FC8008-256-A](#) [FC8008-256-A-24](#) [FC8008-256-SS](#) [FC8009-256-A](#) [FC8009-256-A-24](#) [FC8009-256-SS](#) [FC8010-256-A](#) [FC8010-256-A-24](#) [FC8010-256-SS](#) [FC8011-256-A](#) [FC8011-256-A-24](#) [FC8011-256-SS](#) [FC8012-256-A](#) [FC8012-256-A-24](#) [FC8012-256-SS](#) [FC8013-256-A](#) [FC8013-256-A-24](#) [FC8013-256-SS](#)