



Part Number: DSC2731

Electrical Specifications



Frequency Range (GHz):	27.0 – 31.0
Isolation (dB):	20 MIN
Insertion Loss (dB):	0.6 MAX
VSWR:	1.25:1 MIN
Forward Power (W):	5 AVG
	30 PK

Mechanical/Environmental Specifications


Connector Type:	K (2.92mm)
Connector Body:	Passivated stainless steel
Connector Pin:	Gold plated copper
Load Body:	Brass
Magnetic Shunt:	Nickel plated CRS
Operational Temp:	-15°C to +75°C
Storage Temp:	-40°C to +120°C
Weight (oz):	0.75 MAX
Pressure:	< 1.5e ⁻⁵ torr
Screening Test:	Non-Operational Thermal Cycles
ATP:	Operational thermal cycling

Test Report Included w/CofC. To customize test procedures or specifications to your requirements, please contact DiTom.

DSC2731 Dimensions



DSC2731-3 Dimensions



Dimensions are in inches
Tolerance


XX ±0.03
XXX ±0.010

Type of Device	PN Suffix	Connector Configuration Input / Output	PN Example
Single Junction Circulator 3-Port Device Port 1 / Port 2 / Port 3	No Dash	Female / Female / Female	DSC2731
	-1	Male / Female / Female	DSC2731-1
	-2	Female / Male / Female	DSC2731-2
	-3	Male / Male / Male	DSC2731-3
	-4	Female / Female / Male	DSC2731-4
	-5	Male / Female / Male	DSC2731-5
	-6	Male / Male / Female	DSC2731-6
	-7	Female / Male / Male	DSC2731-7



MEASURED DATA

Part Number: DSC2731, P1→P2, P3 Terminated with 50Ω, +25°C



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DiTom:](#)

[DSC2731](#) [DSC2731-1](#) [DSC2731-2](#) [DSC2731-3](#) [DSC2731-4](#) [DSC2731-5](#) [DSC2731-6](#) [DSC2731-7](#)