



LASC



Single layer

Part No	Inductance L (μH)	f _L (kHz)	Tol ± (%)	DCR max (mΩ)	Rated DC Current (A)
LASC-5R0M-01	5	1000	20	28	6
LASC-6R0M-01	6	1000	20	36	5
LASC-7R0M-01	7	1000	20	42	4
LASC-120M-01	12	100	20	100	3
LASC-200M-01	20	100	20	204	2
LASC-300M-01	30	100	20	420	1.5
LASC-600M-01	60	100	20	924	0.7
LASC-750M-01	75	100	20	1560	0.7
LASC-151M-01	150	100	20	4200	0.4
LASC-161M-01	160	100	20	4560	0.4
LASC-211M-01	210	100	20	7680	0.3
LASC-231M-01	230	100	20	8640	0.3
LASC-421M-01	420	100	20	22800	0.15
LASC-471M-01	470	100	20	24000	0.15

Core Material : Iron Dust

Revision date : 13 Aug 2014

SPQ :	Packing Form	Taped / Reel
	Axial	1000 [-01]

Remarks : - Available also without insulating material (LASC/B).

- Single layer - Model with Insulation Foil
are suitable for application in "Power Line",
rated voltage 230V AC (Test voltage 500V DC).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Fastron:

[LASC-211M-01](#) [LASC-120M-01](#) [LASC-151M-01](#) [LASC-471M-01](#) [LASC-6R0M-01](#) [LASC-5R0M-01](#) [LASC-7R0M-01](#)
[LASC-200M-01](#) [LASC-600M-01](#) [LASC-300M-01](#) [LASC-161M-01](#) [LASC-421M-01](#) [LASC-231M-01](#) [LASC-750M-01](#)