



Representative Image

Alternate Catalog No. S802U-K25
Catalog No. 2CCS862017R0517

Description: MCB S800 2P K 25A

UPC No 7612271214135

Home > Circuit Breakers > Miniature Circuit Breakers > UL 489 Branch Circuit MCBs

S802U-K25 2 Pole K Characteristic 25A 50kA 240/415VAC High Performance Circuit Breaker HPCB

Descriptors

Category	UL 489 Branch Circuit MCBs
----------	----------------------------

Specifications

Number of Poles	2
Tripping Characteristic	K
Rated Current	25 A
Standards	IEC/EN 60947-2 UL 489
Product Main Type	S800U
Rated Voltage (V)	(240 V AC)
Interrupting Rating acc. to UL489	50 kA
Rated Ultimate Short-Circuit Breaking Capacity	(415 V AC) 50 kA
Power Loss	4.2 W

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABB:](#)

[S802U-K25](#)