



Representative Image

Catalog No. RMS212122CHLBR

Description: MTR STACK 1-225A 3PH1PH RNGL LVB 42-100K

UPC No 783164684193

Home > Modular Metering > ReliaMod > ReliaMod Meter Module

Descriptors

Category	ReliaMod Meter Module
----------	-----------------------

Specifications

Enclosure	N3R Outdoor
Meter Equipment Group (MEG) Approved	Yes
Socket Amperage	225 A
Main Phase Input	3-Phase
Socket Phase Output	1-Phase
Voltage	120/240V
Socket Type	Ringless
No of Sockets	1
Socket Factory Installed Jaw Configuration	5-Jaw
Socket Bypass	Lever
Horizontal Bus Amperage	1200 A
Tenant Neutral Lugs (Per each socket) AWG/kcmil Al/Cu	#6-300
Tenant Ground Lugs (Per each socket) AWG/kcmil Al/Cu	#14-2/0
Meter Module Tenant Breaker Provisions	Only Accepts 42-100 KAIC XT3 & XT4 Tenant Breakers
Additional Notes	For tenant breaker load lugs, please refer to breaker specifications
Height (Inches)	54.0
Depth (Inches)	9.7
Width (Inches)	19.6
Estimated Weight (lbs)	167
Meter Mod III to ReliaMod Horizontal Bus Connections	ABB ReliaMod horizontal bus does not match up to GE Meter Mod III horizontal bus, so any ReliaMod section cannot be connected to any GE Meter Mod III section and vice versa without a bus transition adapter section. Please refer to the ReliaMod bus transition adapters in the Buylog for more information.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABB:](#)

[RMS212122CHLBR](#)