



Representative Image

Catalog No. DNR63040

Description: 60A,ILK,3P4W,MG,304,277/480V,NONFSD

UPC No 708917304654

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

Non-Fused Interlocked Receptacle, Voltage 277/480V, Amperage 30A, 3 Poles 4 Wire

Descriptors

Category	Electrical sleeves
----------	--------------------

Specifications

Number Of Poles	3
Number Of Wires	4
Amperage Rating	30 Amps
Voltage Rating	277/480 V

Classifications

Brand Name	Russellstoll
------------	--------------

ETIM Classification

ETIM	EC001322 Round socket/plug for high currents
Amperage	60 A
Number of poles	3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABB:](#)

[DNRF63040](#)