


V1605I-IM-B & R1505I-IM-B

Mini-ITX, AMD Ryzen™ Embedded V/R1000-Series V1605/R1505G APU, 2 x SO-DIMM

Features

- Up to four 4K displays
- Up to 7-year longevity supply
- Wide temperature range endurance: 0~60°C

Specifications




Processor System	APU	AMD Ryzen™ Embedded V1605B/R1505G APUs
Memory	Technology	DDR4 2400MHz, ECC support
	Max.	32GB
	Socket	2 x SO-DIMM
Display	Display Port	3/2, DP++ supports DisplayPort 1.4 with max. resolution 3840x2160 @60Hz (V1605I-IM-B/R1505I-IM-B) 1, DP++ DisplayPort 1.4 with max. resolution 3840x2160 @60Hz (Optional, shared with LVDS and eDP)
	LVDS (default)	1, LVDS supports LVDS with max. resolution 1920 x1200 @60Hz (Optional, shared with DisplayPort1 and eDP)
	eDP (optional)	1, eDP supports eDP 1.3 with max. resolution 3840 x 2160 @ 60Hz (Optional, shared with DisplayPort1 and LVDS)
	Multi Display	Default: • V1605I-IM-B: 3DP+LVDS or 4DP • R1505I-IM-B: 2DP+LVDS or 3DP By request: • V1605I-IM-B: 3DP+eDP • R1505I-IM-B: 2DP+eDP
Expansion Slot	PCIe	1x PCIe 3.0 x8 slot (x8 mode for V1605I-IM-B/ x4 mode for R1505I-IM-B)
	M.2	1 x M.2 Socket 1 with E key, type 2230 (PCIe x1, USB 2.0) (V1605I-IM-B only) 1 x M.2 Socket 3 with M key, type 2242/2260/2280 (PCIe x2, SATA)
Ethernet	Speed	10/100/1000Mbps
	Controller	2 x Realtek® 8111H, support WOL/PXE
	Connector	2 x RJ-45
Audio	Codec	Realtek® ALC 897 codec
	Connector	2 x Audio jacks (1 x Mic-in, 1 x Line-out) 2 x 2W Stereo Speaker output 1 x 5.1 channel (internal pin header)
Storage	Default	1 x SATA port Gen 3.0, up to 6Gb/s 1 x M.2 (Key M, 2242 / 2260 / 2280) PCIe x2 and SATA mode* 1 x CFAST* *If CFAST is enabled, M.2 SATA mode will be disabled, and vice versa. You may configure this setting in the BIOS.
	Per request	2 x SATA port Gen 3.0, up to 6Gb/s 1 x M.2 (Key M, 2242 / 2260 / 2280) PCIe x2
Rear I/O	Display Port	• Default: 3DP+LVDS (V1605I-IM-B) / 2DP+LVDS (R1505I-IM-B) • Optional: 4DP or 3DP+LVDS (V1605I-IM-B) / 3DP or 2DP+eDP (R1505I-IM-B)
	USB 3.2 Gen2 Type-A ports	2 x ports
	USB 2.0 Type-A ports	2 x ports
	Ethernet	2 x RJ45 ports
	Serial Port	2 x COM connectors (support RS232/422/485)
	Audio jack	1 x Mic in 1 x Line out
	Power	1 x DC jack (lockable)


Specifications

Internal Connector	Serial Port	4 x header (RS-232); COM3 colay CCtalk & COM4 colay TTL (BOM option)
	USB 3.2 Gen1	1 x Type A vertical connector (V1605I-IM-B)
	USB 2.0	1 x header support additional 2 x USB2.0 Connectors 1 x type A vertical connector (R1505I-IM-B)
	CPU Fan	1 x header (PWM mode)
	Chassis Fan	1 x header (PWM mode)
	Chassis Intrusion	1 x header
	Front Panel Audio (AAFP)	2 x headers
	System Panel Header	1 x header
	Clear CMOS Jumper	1 x header
	SATA power	2 x header
	LPC Debug	1 x header
	S/PDIF	1 x header
	I ² C	1 x header
	GPIO	1 x header
	AT/ATX Select	1 x header
	Power Connector	1 (4 pin)
Watchdog Timer	H/W	Yes
Security	TPM	1 x SPI TPM header
Power	Power Type	DC-in (ATX and AT mode supported)
	Voltage	DC-in 12V ~ 24V
Operating System	Microsoft Windows	Windows® 10 (64bit) / Win10 IoT Enterprise
	Linux	Ubuntu, RedHat Enterprise, Fedora Workstation, OpenSUSE
Environment	Operating Temperature	0~60° C
	Non-Operating Temperature	-40~85° C
	Relative Humidity	5%~95%
Dimension	Form Factor	Mini-ITX, 170 x 170 mm
Certification	Safety	CE, FCC

Block Diagram



Block Diagram



Order Information

Model name	Part number	Description
V1605I-IM-B	90ME02V0*	SOC, V1605, 3*DP, LVDS
V1605I-IM-B	90ME02V1*	SOC, V1605, 4*DP
R1505I-IM-B	90ME02W0*	SOC, R1505, 2*DP, LVDS
R1505I-IM-B	90ME02W2*	SOC, R1505, 3*DP

* The part number might vary for different regulations and package. Please consult the TPM in your region for exact 90PN.

Packing List

Part number	Description	Quantity
13020*	IO shield	1
14013*	SATA 6G CABLE	1
13020*	M.2 screw pack	1
13071*	Fansink backplane	1
13070*	Fansink	1

* The part number might vary due to part number revision.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Asus:](#)

[90ME02V0-M0UCY0](#) [V1605I-IM-B](#)