


H610I-IM-A

Mini-ITX, LGA1700 socket for the 14/ 13/ 12th Gen CPU, H610 chipset,
2*SO-DIMM, 1*PCIe x16, 1*DP, 2*HDMI, 1*LVDS, 2*M.2 slot.

Features

- Support up to 65W Intel® 14th/ 13th/ 12th Gen. CPU
- Two SO-DIMM up to 64GB DDR4 3200 MHz
- Supports multiple displays: LVDS/ HDMI/ DP
- 7-year longevity supply




Specifications

Processor System	CPU	LGA1700 for Intel® 14 th / 13 th / 12 th Gen. Core™ i9/ i7/ i5/ i3/ Pentium®/ Celeron® Processors Max. 65W TDP
	Chipset	Intel® H610 Chipset (IoTG)
Memory	Technology	DDR4
	Max.	2 x 32GB (Total 64GB)
	Socket	2 x SO-DIMM
Display	DP	1
	HDMI	2
	LVDS	1
	Multiple displays	Max. 3 displays
Expansion Slot	PCIe	1 x PCIe 4.0 x16 Slot
	M.2	1 x M.2 E key, Type 2230 for WIFI/ BT device (PCIe & CNVi) 1 x M.2 M key, Type 2242/ 2260/ 2280 (PCIe x4/ SATA mode)
Ethernet	Speed	10/ 100/ 1000 Mbps
	Controller	1 x Intel® i210AT, 1 x Intel® i219V
	Connector	2 x RJ-45
Audio	Codec	Realtek ALC897
Storage	SATA port	3x SATA Gen 3.0, up to 6Gb/s
Rear I/O	Display Port	1
	HDMI	2
	USB 3.2 Gen1	4
	Ethernet	2 x RJ45
	Serial Port	2 (RS232/ 422/ 485)
	Audio jack	2 (Line-Out, mic-in)
Internal Connector	COM Header	4 x COM Header (RS232)
	USB2.0	2 x Header Support Additional 4 x USB 2.0 Ports
	CPU Fan/ Chassis Fan	1 x Header (PWM Mode)/ 1 x Header (PWM Mode)
	LVDS/ eDP selection	1 x Header
	Panel SW	1 x Header
	Front Panel Audio (AAFP)	1 x Header
	System Panel	1 x Header
	Chassis Intrusion	1 x Header
	Speaker connector	1 x Header
	Clear CMOS	1 x Header
	COM Debug	1 x Header
	GPIO	1 x Header (8 Bit)

Watchdog Timer	H/W	YES
Security	TPM	1 x SPI TPM header
Power Type	Power Type	ATX, 12V DC-IN (*Support by power transfer card "EMA-DCB-A".)
OS & Software Support	Microsoft Windows	Windows® 10 (64bit)
	Linux	Ubuntu, RedHat Enterprise, Fedora Workstation, OpenSUSE
	ASUS IoT Suite	☒ HW Monitor ☒ Power Scheduling ☒ Fan Control ☒ Watch Dog Timer ☒ GPIO
	User Interfaces	☒ API ☒ GUI
Environment	Operating Temperature	0~60° C
	Non-Operating Temperature	-40~85° C
	Relative Humidity	Operational humidity: 40°C@10%~95%
Mechanical	Dimensions	Mini-ITX, 170 x 170 mm
Certification	EMC (CLASS B)	CE, FCC, BSMI, VCCI
	Safety	CE-LVD

Block Diagram



Order Information

Model name	Part number	Description
H610I-IM-A	90ME064*	LGA1700, H610, DP, HDMI, LVDS

* The part number might vary for different regulations and package. Please consult the TPM in your region for exact 90PN.

Packing List

Part number	Description	Quantity
13020*	IO shield	1
14013*	SATA 6G CABLE	1
13020*	M.2 SCREW PACK	1

* The part number might vary due to part number revision.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Asus:](#)

[90ME0640-M0UCY0](#) [H610I-IM-A](#)