

## Product data sheet

### Characteristics

## 9007HA2

limit switch lever arm, 9007C, nonbendable  
adjustable lever arm, 0.625 inch diameter  
roller, 0.625 inch wide roller



### Main

|                             |                                                                                      |
|-----------------------------|--------------------------------------------------------------------------------------|
| Range of Product            | 9007                                                                                 |
| Series name                 | Heavy duty                                                                           |
| Product or Component Type   | Limit switch lever                                                                   |
| Device short name           | 9007C                                                                                |
| Associated head             | 9007T5<br>9007N<br>9007B<br>9007T10<br>9007C<br>9007A                                |
| Associated complete product | 9007C<br>9007AW                                                                      |
| Movement of operating head  | Rotary                                                                               |
| Type of operator            | Cast zinc spring return adjustable roller lever 0.88... 4 in (22.35...101.60 mm) - - |
| Type of roller              | 1 steel outside roller 0.63 in (16.00 mm) 0.63 in (16.00 mm)                         |
| Type of approach            | Lateral approach                                                                     |
| Positive opening            | Without                                                                              |

### Complementary

|                  |                      |
|------------------|----------------------|
| Switch actuation | By 30° cam           |
| Net Weight       | 0.1 lb(US) (0.05 kg) |

### Environment

|                                       |                            |
|---------------------------------------|----------------------------|
| Ambient Air Temperature for Operation | -20...185 °F (-29...85 °C) |
| Ambient Air Temperature for Storage   | -20...185 °F (-29...85 °C) |
| Environmental characteristic          | Standard environment       |

### Ordering and shipping details

|                       |                          |
|-----------------------|--------------------------|
| Category              | 21493-9007 ARMS FOR AW,C |
| Discount Schedule     | DS1                      |
| GTIN                  | 785901743910             |
| Nbr. of units in pkg. | 1                        |
| Package weight(Lbs)   | 2.40 oz (68.0 g)         |
| Returnability         | Yes                      |
| Country of origin     | MX                       |

### Packing Units

|                        |                   |
|------------------------|-------------------|
| Unit Type of Package 1 | PCE               |
| Package 1 Height       | 0.91 in (2.3 cm)  |
| Package 1 width        | 4.02 in (10.2 cm) |
| Package 1 Length       | 7.99 in (20.3 cm) |

## Offer Sustainability

|                            |                                                                                                                                                                                                                                                                                                                                                                                   |
|----------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                                                                                                                                                                                                             |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                                                                                                                                 |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                                                                                                                    |
| Mercury free               | Yes                                                                                                                                                                                                                                                                                                                                                                               |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                                                                                                                                               |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                                                                                                                                                     |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[9007HA2](#)