

Product data sheet

Characteristics

TCSEL1F3M125S2D

Shielded twisted pair straight cable,
ConneXium, M12 to RJ45, 24 AWG, PVC, 25
m



Main

Range of product	ConneXium
Accessory / separate part category	Connection accessories
Accessory / separate part type	Connecting cable
Product or Component Type	Shielded twisted pair straight cable
Accessory / separate part destination	Ethernet network

Complementary

Marking	UL
Cover Material	PVC

Environment

IP degree of protection	IP20
-------------------------	------

Ordering and shipping details

Category	22499 - SENSORS ACCESSORIES
Discount Schedule	DS2
GTIN	03389119130714
Nbr. of units in pkg.	1
Package weight(Lbs)	2.5 lb(US) (1.13 kg)
Returnability	No
Country of origin	DE

Packing Units

Package 1 Height	1.00 in (2.540 cm)
Package 1 width	12.00 in (30.480 cm)
Package 1 Length	12.00 in (30.480 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[TCSEL1F3M125S2D](#)