

Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

|                   |            |
|-------------------|------------|
| Body type         | Standard   |
| Device short name | AW         |
| Series name       | Heavy duty |

### Complementary

|                            |                               |
|----------------------------|-------------------------------|
| Line Rated Current         | 15 A                          |
| Body material              | Cast zinc                     |
| Contact operation          | Snap action                   |
| Fluid connection type      | 0.5 inch BSP conduit entrance |
| Maximum displacement angle | 30 °                          |
| Switch actuation           | CCW                           |
| Tilting angle              | 5 °                           |
| Torque value               | 2.75 lbf.in                   |
| Tripping angle             | 2.5 °                         |

### Environment

|                                       |   |
|---------------------------------------|---|
| Ambient air temperature for operation | -60...185 °F  |
| NEMA degree of protection             | NEMA 1/2/4/12/13  |
| Product certifications                | CE<br>CSA LR25490 class 3211 03<br>UL listed file E42259 CCN NKCR |

### Ordering and shipping details

|                       |  |
|-----------------------|--|
| Category              | 21496 - 9007 AW PRECISION LIMIT SWITCHES |
| Discount Schedule     | DS1                                      |
| GTIN                  | 00785901607632                           |
| Nbr. of units in pkg. | 1  |
| Package weight(Lbs)   | 1.25                                     |
| Returnability         | N  |
| Country of origin     | MX                                       |

### Offer Sustainability

|                                  |   |
|----------------------------------|---|
| RoHS (date code: YYWW)           | Will not be compliant   |
| REACH                            | Reference not containing SVHC above the threshold   |
| Product environmental profile    | Available   |
| Product end of life instructions | Need no specific recycling operations   |
| California proposition 65        | WARNING: This product can expose you to chemicals including:                                |
| - - - - - Substance 1            | Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and |

|                        |  |
|------------------------|--|
| ----- Substance 2      | Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. |
| ----- More information | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>                              |

### Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[9007AW12M16](#)