

ZCKD23

Limit switch head, Limit switches XC Standard, ZCKD, steel roller lever plunger



Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCKD
Head type	Plunger head
Product Compatibility	XCKM XCKL
Associated body	ZCKMD37H7 ZCKMD31H29 ZCKM6H29 ZCKM1H29 ZCKMD37H29 ZCKM9 ZCKM8H7 ZCKL5H7 ZCKL6 ZCKM6 ZCKLD39 ZCKL1 ZCKM1H7 ZCKM5 ZCKM8H29 ZCKLD37H7 ZCKL1H7 ZCKLD39H7 ZCKM6H7 ZCKM1 ZCKMD35H29 ZCKL7H7 ZCKMD39 ZCKM8 ZCKMD31H7 ZCKMD39H29 ZCKLD35 ZCKMD37 ZCKM7 ZCKLD37 ZCKMD39H7 ZCKM9H29 ZCKMD31 ZCKL5 ZCKL6H7 ZCKLD31H7 ZCKMD35 ZCKM7H29 ZCKM5H29 ZCKLD35H7 ZCKMD35H7 ZCKL8 ZCKM5H7 ZCKL7 ZCKLD31 ZCKL8H7 ZCKM7H7
Movement of operating head	Rotary Linear
Type of operator	Roller lever plunger spring return metal
Type of approach	Lateral approach, 1 direction

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Complementary

Switch actuation	By 30° cam
Positive opening	With
Head material	Plastic

Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22416-LIMIT SWITCHES,IEC,XCKL
Discount Schedule	T
GTIN	3389110646733
Returnability	Yes
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.38 in (3.5 cm)
Package 1 Width	2.56 in (6.5 cm)
Package 1 Length	2.99 in (7.6 cm)
Package 1 Weight	3.42 oz (97 g)
Unit Type of Package 2	S01
Number of Units in Package 2	28
Package 2 Height	5.91 in (15 cm)
Package 2 Width	5.91 in (15 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	6.64 lb(US) (3.011 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[ZCKD23](#)