

ZCKE055

Limit switch head, Limit switches XC Standard,
ZCKE, without lever left and right actuation,
+120 °C





Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCKE
Head type	Rotary head
Product Compatibility	XCKJ
Associated lever	ZCKY52 ZCKY11 ZCKY43 ZCKY59 ZCKY81 ZCKY41 ZCKY14 ZCKY91 ZCKY53 ZCKY13 ZCKY51
Associated body	ZCKJ7H29 ZCKJ6H29 ZCKJ404H7 ZCKJ9H7 ZCKJ11H7 ZCKJ41 ZCKJ6H7 ZCKJ11 ZCKJ7H7 ZCKJ9H29 ZCKJ2H7 ZCKJ4104H7 ZCKJD39 ZCKJD35H7 ZCKJD31H7 ZCKJ7 ZCKJ1H7 ZCKJ21 ZCKJ8 ZCKJ21H7 ZCKJ8H29 ZCKJ4H29 ZCKJD35H29 ZCKJ5H7 ZCKJD39H7 ZCKJ8H7 ZCKJ5H29 ZCKJ4H7 ZCKJD35 ZCKJ1H29 ZCKJ21H29 ZCKJ9 ZCKJD37 ZCKJ6 ZCKJ41H7 ZCKJD37H29 ZCKJ2 ZCKJ4104H29 ZCKJD37H7 ZCKJD31 ZCKJ2H29 ZCKJ5 ZCKJ4 ZCKJ1 ZCKJ41H29 ZCKJ4104 ZCKJD31H29 ZCKJ11H29 ZCKJ404H29 ZCKJD39H29 ZCKJ404
Movement of operating head	Rotary

Type of operator	Without operating lever spring return
Type of approach	Lateral approach, 1 or 2 programmable direction

Complementary

Switch actuation	From left and/or right CW and/or CCW
Positive opening	With
Net Weight	0.36 lb(US) (0.165 kg)
Head material	Metal

Environment

Ambient Air Temperature for Operation	50...248 °F (10...120 °C)
Ambient Air Temperature for Storage	50...248 °F (10...120 °C)
Environmental characteristic	High temperature

Ordering and shipping details

Category	22411-LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	3389110599374
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.57 in (4 cm)
Package 1 Width	2.44 in (6.2 cm)
Package 1 Length	4.49 in (11.4 cm)
Package 1 Weight	6.00 oz (170 g)
Unit Type of Package 2	S01
Number of Units in Package 2	27
Package 2 Height	5.91 in (15 cm)
Package 2 Width	5.91 in (15 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	10.87 lb(US) (4.932 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[ZCKE055](#)