

# ZCKM1H7

Limit switch body, Limit switches XC Standard, ZCKM, 1NC+1 NO, snap action, 1/2"NPT



## Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch body
Device short name	ZCKM
Body type	Fixed
Product Compatibility	XCKM
Associated head	ZCKD239 ZCKD029 ZCKD17 ZCKD41 ZCKD08 ZCKD06 ZCKD05 ZCKD91 ZCKD219 ZCKD16 ZCKD23 ZCKD21 ZCKD15 ZCKD02 ZCKD10 ZCKD59 ZCKD109 ZCKD81
Body Material	Metal
Cable entry	3 entries tapped for Pg 11 cable gland, one with 1/2" NPT adaptor
Number of poles	2
Contacts type and composition	1 NC + 1 NO
Contact operation	Snap action
Number of steps	1 1 position
Contacts material	Silver plated contacts

## Complementary

Local display	Without
Electrical connection	Screw-clamp terminals 1 x 0.34...2 x 1.5 mm <sup>2</sup>
Positive opening	With
Minimum actuation speed	0.01 m/min
[Ie] rated operational current	3 A 240 V, AC-15, A300 EN/IEC 60947-5-1 appendix A 0.27 A 250 V, DC-13, Q300 EN/IEC 60947-5-1 appendix A
[Ithe] conventional enclosed thermal current	10 A
[Ui] rated insulation voltage	500 V 3) IEC 60947-1 contact block 300 V CSA C22.2 No 14 contact block 300 VUL 508 contact block
Maximum resistance across terminals	0.25 mOhm IEC 60255-7 category 3
[Uimp] rated impulse withstand voltage	6 kV IEC 60664 6 kV IEC 60947-1
Short-circuit protection	10 A cartridge fuse gG
Electrical durability	5000000 Cycles, DC-13 120 V, 7 W 60 cyc/mn 0.5 IEC 60947-5-1 appendix C 5000000 Cycles, DC-13 24 V, 13 W 60 cyc/mn 0.5 IEC 60947-5-1 appendix C 5000000 cycles, DC-13 48 V, 9 W 60 cyc/mn 0.5 IEC 60947-5-1 appendix C
Width	2.52 in (64 mm)

Height	2.52 in (64 mm)
Depth	1.18 in (30 mm)
Net Weight	0.46 lb(US) (0.21 kg)
Terminals description ISO n°1	(13-14)NO (21-22)NC

## Environment

IP Degree of Protection	IP66
IK Degree of Protection	IK05
Ambient air temperature for operation	-13...158 °F (-25...70 °C) standard environment
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment





## Ordering and shipping details

Category	22416-LIMIT SWITCHES,IEC,XCKL
Discount Schedule	T
GTIN	3389118130128
Nbr. of units in pkg.	1
Package weight(Lbs)	9.66 oz (274.0 g)
Returnability	Yes
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.26 in (3.2 cm)
Package 1 width	5.67 in (14.4 cm)
Package 1 Length	2.52 in (6.4 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	32
Package 2 Weight	20.79 lb(US) (9.431 kg)
Package 2 Height	5.91 in (15.0 cm)
Package 2 width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[ZCKM1H7](#)