

ZCMD25

Limit switch body, Limit switches XC Standard, ZCMD, 1NC+1 NO, silver, slow break



Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch body
Device short name	ZCMD
Design	Miniature
Body type	Plug-in body
Associated head	ZCE66 ZCE28 ZCEG1 ZCE02 ZCE01 ZCE27 ZCE13 ZCE11 ZCE64 ZCEH0 ZCE62 ZCE14 ZCE06 ZCE65 ZCE05 ZCE29 ZCE67 ZCEH2 ZCE07 ZCE08 ZCEF0 ZCE24 ZCEF2 ZCE10 ZCE21 ZCE63
Body Material	Zamak
Number of poles	2
Contacts type and composition	1 NC + 1 NO
Contact operation	Slow-break, break before make

Complementary

Product Compatibility	XCMD
Associated connection component	ZCMC25E2 ZCMC25L1 ZCMC25E3 ZCMC25L7 ZCMC25L5 ZCMC25E10 ZCMC25E1 ZCMC25L10 ZCMC25E7 ZCMC25L2 ZCMC25E5 ZCMC25T06 ZCMC25L3
Electrical connection	Plug-in without pre-cabled connection
Contacts insulation form	Zb
Contacts material	Silver plated contacts
Positive opening	With

Minimum actuation speed	6 m/min
Contact code designation	B300, AC-15 (Ue = 240 V), Ie = 1.5 A EN/IEC 60947-5-1 appendix A R300, DC-13 (Ue = 250 V), Ie = 0.1 A EN/IEC 60947-5-1 appendix A
[Ui] rated insulation voltage	300 V 3)UL 508 400 V 3)IEC 60947-5-1 300 V 3)CSA C22.2 No 14
Maximum resistance across terminals	25 mOhm IEC 60255-7 category 3
[Uimp] rated impulse withstand voltage	4 kV IEC 60664 4 kV IEC 60947-1
Short-circuit protection	6 A cartridge fuse gG
Electrical durability	5000000 Cycles, DC-13 120 V, 3 W 60 cyc/mn 0.5 IEC 60947-5-1 appendix C 5000000 Cycles, DC-13 24 V, 4 W 60 cyc/mn 0.5 IEC 60947-5-1 appendix C 5000000 cycles, DC-13 48 V, 3 W 60 cyc/mn 0.5 IEC 60947-5-1 appendix C
Width	1.18 in (30 mm)
Height	1.97 in (50 mm)
Depth	0.63 in (16 mm)

Environment

Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
-------------------------------------	----------------------------

Ordering and shipping details

Category	22413-LIMIT SWITCH, IEC, MINIATURE
Discount Schedule	T
GTIN	3389110299106
Returnability	Yes
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.63 in (1.6 cm)
Package 1 Width	2.09 in (5.3 cm)
Package 1 Length	1.18 in (3.0 cm)
Package 1 Weight	1.98 oz (56.0 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[ZCMD25](#)