

4

3

2

1

D

D

C




C

B

B

A

A

**NOTES:**

1. Unless otherwise noted, dimensions are in inches.
2. Shell: 360 brass, half-hard, with 10 μ m gold over nickel
3. Contacts: Beryllium copper with 30 μ m gold over nickel
4. Current rating: 8 amps, for 10°C temperature rise.
5. Solder mount in minimum .075 diameter mounting hole.
6. Mill-Max Part No. 0329-0-15-15-34-27-10-0

TOLERANCES - UNLESS
OTHERWISE SPECIFIED

.XX = $\pm$.01 [.254]
.XXX = $\pm$.005 [.127]
ANG. = $\pm$ 5°



TITLE:

PIN RECEPTACLE
FOR .032-.046 DIAMETER PINS

MODEL:

MS02

SUBJECT:

MECHANICAL DRAWINGENGINEER:
D-MDRAWN BY:
R.MORDCA:
13241SHEET
1 OF
1FILENAME:
MS02REV:
DDATE:
03JUN13

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Apex Microtechnology:](#)

[MS02](#)