

FLUKE®

88 Series V/A Automotive Meter Combo Kit

The Fluke 88V/A Kit is a complete automotive diagnostic package. It offers virtually everything you need in an automotive multimeter.

Features

- 0.1 % dc accuracy
- 4-1/2 digit mode for precise measurements (20,000 counts)
- Measure up to 1000 V ac and dc
- Current measurements up to 10 A, 20 A for up to 30 seconds
- Built-in thermometer for temperature measurements when you need them (temperature probe included)
- Resistance, continuity and diode test
- RPM measurements with inductive pickup (included)
- Millisecond pulse width measurements for fuel injectors
- Magnetic hanger to attach meter to the vehicle and free your hands for other tasks
- Min/Max/Average recording with Min/Max Alert to capture variations automatically
- Peak Min/Max to record transients as fast as 250 μ s
- Relative mode to remove test lead resistance from low ohms measurements
- Auto and manual ranging for maximum flexibility
- Autohold™ to capture stable readings with only one touch of the leads
- Large display digits and two-level bright white backlight for increased visibility
- Analog bargraph to track changing or unstable signals
- Input Alert provides audible warning against wrong use of input jacks
- Access door for fast battery changes without opening up the case
- "Classic" design that fits your hand with new removable holster, built-in test lead and probe storage
- 10 meg ohm input impedance won't damage computer circuits
- Limited lifetime warranty on meter, 1 year on accessories

Specifications

| Basic Accuracy (\pm % of reading) | | | |
|--------------------------------------|-------------------------------|----------|-----------------|
| Function | Range | Accuracy | Best Resolution |
| DC Voltage | 600 mV to 1000 V | 0.1 % | 0.01 mV |
| AC Voltage | 600 mV to 1000 V | 0.5 % | 0.01 mV |
| DC Current | 60 mA to 10 A | 0.4 % | 0.001 mA |
| AC Current | 60 mA to 10 A | 1.2 % | 0.001 mA |
| Ohms | 600 Ω to 50 M Ω | 0.4 % | 0.01 Ω |
| Frequency | 199.99 Hz to 199.99 kHz | 0.005 % | 0.01 Hz |



Powerful magnet holds meter to most steel surfaces



88V/A Automotive Meter Combo Kit Includes

- 88V Automotive Multimeter
- TL224 1.5 m long heat resistant silicone test leads
- TP220 removeable test probes to correctly measure corroded terminals
- AC285 Alligator Clips
- TPAK Magnetic Hanger to position and hold meter to steel surfaces
- 80BK Temperature Probe
- RPM80 Inductive Pick-Up Probe
- 2 Automotive Back Probe Pins
- Insulation Piercing Probe
- C800 Durable Carrying Case

Ordering information

Fluke-88-V/A Automotive Meter Combo Kit

Optional accessories

| Model | Description | |
|-------------|---|---|
| TLK281 | SureGrip™ Automotive Test Lead Kit | Complete set of test and measurement accessories designed especially for automotive specialists. |
| TLK282 | SureGrip™ Deluxe Automotive Test Lead Kit | Everything you can find in the TLK281 Automotive Test Lead Kit, plus a few extras. |
| TP81 & TP82 | Insulation Piercing Probes | Set of stainless steel probe pierces insulation on 14, 16 and 18 gauge wire. Essential for use under hood or under dash. Use it on fuel injectors or sensors while providing complete insulation to grounding due to design. |
| TP40 | Automotive Back Probe Pins | Set of five flexible and formable 1-1/4 inch pin provides an easy connection past weather pack seals to connector conductors. A must-have for fuel injectors, TPS and MAP sensors, as well as for any underhood or under vehicle connector with weather pack seals. |
| TP88 | Rigid Back Probe Pins | Set of one red and one black two inch long rigid back probe pins easily pass between the weather pack seal and wire. A sharp point ensures good contact to the electrical connector, and the pin's insulation protects it from shorting to other wires. |
| TP84 | Oxygen Sensor Insulation Piercing Probes | 12 inch long piercing probe extends your reach into a hot engine. Foot-long probe keeps your hands away from the exhaust manifold. |
| PV350 | Pressure Vacuum Transducer | Use your general purpose meter to read compression, static or running, as well as air pressure, engine vacuum, transmission pressures as well as fuel pressure. |

Fluke. *Keeping your world up and running.*

Fluke Corporation
PO Box 9090, Everett, WA USA 98206

Fluke Europe B.V.
PO Box 1186, 5602 BD
Eindhoven, The Netherlands

For more information call:
In the U.S.A. (800) 443-5853 or
Fax (425) 446-5116
In Europe/M-East/Africa (31 40) 2 675 200 or
Fax (31 40) 2 675 222
In Canada (800)-36-FLUKE or
Fax (905) 890-6866
From other countries +1 (425) 446-5500 or
Fax +1 (425) 446-5116
Web access: <http://www.fluke.com/>

©2004 Fluke Corporation. All rights reserved.
Printed in U.S.A. 8/2004 2085038 D-US-N Rev B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Fluke:

[FLUKE-88-5/A KIT](#)