

Carrying Case Selection Guide

CC-ACDC

Soft pouch zippered
Carrying Case
11.5 x 4.5 x 2.8"
(292 x 114 x 70 mm)



DC205C

Deluxe Heavy Duty
Carrying Case
9.6 x 4.7 4.3"
(244 x 119 x 109 mm)



CC-MEG

Soft Carrying Case
10 x 8.5 x 3.25"
(254 x 216 x 89 mm)



SV-U

Soft pouch zippered
Carrying Case
8.5 x 3.0 x 2.5"
(216 x 76 x 64 mm)



VC221B

Padded vinyl
Carrying Case
8.5 x 4.5 x 2.5"
(216 x 114 x 64 mm)



VC3A

Rugged zippered
Carrying Case
4.5 x 2.2 x .4"
(114 x 56 x 10mm)



VC30A

Vinyl Carrying Case
7.5 x 3.4 x 1.5"
(191 x 86 x 38 mm)



CC-DM-III

Deluxe Heavy Duty
Carrying Case
18.3 x 15.0 x 7.3"
(465 x 381 x 184 mm)



CC-300 PRO

Leather Carrying Case
10.84 x 4.20 x 2.40"
(275 x 107 x 70 mm)



	CC-ACDC	DC205C	CC-MEG	SV-U	VC221B	VC3A	VC30A	CC-DM-III	CC-300PRO
30XR-A		•							
33XR-A		•							
34XR-A		•							
37XR-A		•							
38XR-A		•							
5XP-A							•		
15XP-B							•		
35XP-A							•		
AC40C	•								
AC50A	•								
AC68C	•								
AC75B	•								
ACD-50NAV	•								
ACD-51NAV	•								
ACDC-52NAV	•								
ACD-53NAV	•								
ACDC-54NAV	•								
ACD-20SW	•								
ACD-21SW	•								
ACD-22SW	•								
ACD-23SW	•								
ACD-10 PLUS				•					
ACD-10 TRMS PLUS				•					
ACD-14 PLUS				•					
ACD-14 TRMS-PLUS				•					
ACD-15 TRMS-PRO				•					
ACD-16 TRMS-PRO				•					
ACD-41PQ				•					
ACD-45PQ				•					
ACD-6 PRO				•					
ACDC-100				•					
ACDC-100 TRMS				•					
ACD-3300 IND	•								
ACDC-3400 IND	•								
ACDC-400	•								
AD40B	•								
AM-140-A	•								
AM-160-A	•								
AM-220							•		
AM-240							•		
AM-250		•			•				
AM-270		•			•				
AM8C		•			•				
CR50A							•		
DGC-1000A		•							
DM73C	•								
DM78C	•								
DM7C		•			•				
DM9C		•			•				
HD110C		•			•				
HD160C		•			•				
INSP-3		•			•				
LCR55A		•			•				
LH41A				•					
PMS1A						•			
PM55A						•			
RS-1007	•								
RS-3 PRO	•								
TIC 300 PRO									•
GP2			•						
DM III Multitest								•	
AMB-45			•						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AMPROBE:](#)
[CC-MEG CASE](#)