



FEATURES:

- Multi-purpose test clips allow five ways to connect to a device under test
 - U-shaped nose for blade shaped terminals
 - Notched jaw for gripping screw heads, bare wire or terminals
 - Serrated teeth for gripping threaded or wire wrapped terminals
 - Cluster of sharp needles for piercing small gauge wires (#22-28 AWG)
 - Large piercing needle for penetrating large gauge wires

MATERIALS:

Jaws: Non-rusting Nickel Copper Alloy

Boot: Vinyl

Wire: 18 AWG , Silicone, 0.144" outside diameter

Banana Plug:

Spring: Beryllium Copper, nickel plated

Body: Brass Nickel Plated

Insulation: Polypropylene

RATINGS:

Operating Voltage: Hand-held 30 VAC/60 VDC

Hands free operation in a controlled voltage environment: 300 VRMS

Current: 8 Amperes

ORDERING INFORMATION: Model 6483-48-*

*=Color; 0-Black, 2-Red, -02 set (1 Black and 1 red lead)

Standard Length = 48" (1219,0)

All dimensions are in inches. Tolerances (except noted): .xx = \pm .02" (.51 mm), .xxx = \pm .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

6483-48-02