

AMPROBE®

DM-CT-100 Current Transducer



- Optional accessory for Amprobe digital recorders*
- Current measurement from 0.5A to 100A
- Maximum conductor size:
diameter 0.59" (15mm)
bus bar 0.59" (15mm) x 0.67" (17mm)
- Output sensitivity 10mV / A
- Basic accuracy:
0.5A to 10A +/- (3% + 5 mV)
10A to 50A +/- (2% + 5 mV)
50A to 100A +/- (1% + 5 mV)
- Safety: CAT III 600V

**Verify recorder compatibility with Amprobe catalog or on our website: www.Amprobe.com*

General Data	
Maximum conductor size	15mm diameter, bus bar 15x17mm
Operating/ Storage Temperature	-10°C to +55°C / -20°C to +70°C (14°F to 131°F/-4°F to 158°F)
Enclosure Protectio	IP20 (EN 60529)
Weight	175 g
Output Connection	2m lead with D01 connector
Overheating will occur if the product is subjected to	(I _p rms x frequency) > 1,000,000. Limit measurement time
Power measurement	Respect the conventional P1=S1 direction of the arrow on the probe. (see drawing)



Miramar, FL 33025 • Toll Free: 800-327-5060 • Phone: 954-499-5400 • Fax: 866-287-7222 • www.Amprobe.com

www.AMPROBE.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AMPROBE:](#)

[DM-CT-100](#)