



AC40B Clamp Type Digital Multimeter

- Mini-clamp DMM
- 400 A range
- 10mA resolution
- 600 V AC and DC range
- 4000-count display with bargraph
- Autoranging
- Data Hold
- Auto-off
- CAT III 600 V rated

Included Accessories

Users Manual, carrying case, test leads

Optional Accessories

DL243D Basic Test Lead Kit
DL248D Deluxe Test Lead Kit
TL35B Test Lead Set with Alligator Clips

No hassle warranty

No waiting.

*No shipping
charges.*



Our commitment to high-quality products and customer service is demonstrated by our industry exclusive "No Hassle" warranty. In the unlikely event that an Amprobe Test Tool requires warranty service, any of our local dealers are authorized to replace it, on the spot.

(note: \$500 MSLP limit)





AC40B Clamp Type Digital Multimeter

Data Sheet

General Specifications

Display:	3-3/4 digit LCD (max reading 3999)
Overrange Indication:	"OL" indicated
Low Battery Indication:	Battery symbol appears when battery power is low
Power Supply:	Two (2) 1.5 V AAA batteries (UM-4)
Battery Life:	Alkaline 300 hours, approx.
Maximum Jaw Opening:	25.4 mm
Dimensions (WxHxD):	64 x190 x 36 mm
Weight:	280 g (incl. battery)
Operating Temperature:	0 °C to + 40 °C, < 80 % R.H. noncondensing
Storage Temperature:	- 10 °C to + 60 °C, < 70 % R.H. non-condensing, batteries removed
Warranty:	One-year

Specifications (23 °C ± 5 °C, < 80 % R.H. non-condensing)

Function	Range	Accuracy
DC Voltage		
Ranges	400 V, 600 V	Accuracy ± (1.2 % rdg + 5 dgts)
Resolution	0.1 V in 400 V range	
Input Impedance	1 MΩ	
AC Voltage (50-400 Hz)		
Ranges	400 V, 600 V	± (1.5 % rdg + 10 dgts)
Resolution	0.1 V in 400 V range	
Input Impedance	1 MΩ	
AC Current		
Ranges	40 A, 400 A	± (2 % rdg + 10 dgts)
Resolution	0.01 A in 40 A range	
Resistance		
Range	400 Ω	± (1 % rdg + 5 dgts)
Resolution	0.1 Ω in 400 Ω	
Continuity (audible)		
Continuous Tone and •)))	Display at R < 40 Ω	
Max Open Voltage	- 1.2 V	
Overload Protection		
660A for AC current only		
660V RMS for all other measurements		

Amprobe® Test Tools
website: www.Amprobe.com
email: info@amprobe.com
Everett, WA 98203
Tel: 877-AMPROBE

Amprobe® Test Tools Europe
In den Engematten 14
79286 Glottertal, Germany
Tel.: +49 (0) 7684 8009 - 0

©2007 Amprobe Test Tools. All rights reserved.
9/2007 1646535 D-US-N Rev C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AMPROBE:](#)

[AC40B](#)