



### FEATURES:

- Mates to Model #1581, 2854 or standard Banana Jack.
- Cross and vertical stacking banana plug.
- Ideal for providing jumpers or chassis boxes.

### MATERIALS:

Conn: Extension Stacking Banana Plug

Material: Spring, Beryllium Copper per QQ-C-533, Allow 172, Cond. HT.

Plug Body: Brass, per QQ-B-626, Alloy 360, ½ hard.

Finish: Nickel plate per QQ-N-290 class 2, 200/300 microinches.

Insulation: Polypropylene molded to plug body and wire

Color: Matches color of wire.

Marking: "MODEL B-XX"

Wire: 18 AWG, stranding 65 x 36 t.c., PVC insulated, 3.66 (.144) O.D.

Color: See Ordering Information

Marking: "POMONA B-XX-\*"

### RATINGS: (Entire Assembly)

Operating Temperature.: +55°C. (+131°F.) Max.

Operating Voltage: Hand-held Testing: 30VAC/60 VDC Max.

Hands free testing in Controlled Voltage Environment: 5000 WVDC

Current: 15 Amperes Cont.

### ORDERING INFORMATION: Model B-XX-\*

XX = Cable Lengths, Standard Lengths: 4" (102), 8" (203), 12" (305), 18" (457), 24" (610), 36" (914), 48" (1219), 60" (1524) & 72" (1829). Additional lengths can be quoted upon request.

\*= Color, -0 Black, -1 Brown, -2 Red, -3 Orange, -4 Yellow, -5 Green, -6 Blue, -7 Violet, -8 Gray, -9 White

Ordering Example: B-72-2 Indicates 72" in length, Color is Red.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[4578#/BULK](#) [B-60-0#](#)