


## Model 1269 BNC (Female) To Double Stacking Banana Plugs



### FEATURES:

- Adapter converts Double Banana Jack Test Instruments to BNC Coaxial configuration for added shielding protection.
- For test versatility, banana plugs can be vertically and horizontally stacked to the adapter.
- Banana Plug features Nickel Plated, Beryllium Copper for tarnish resistance & long insertion life.
- The BNC center contact is Gold Plated, Beryllium Copper for low contact resistance
- The BNC shell is plated for tarnish resistance.

### MATERIALS: BNC (Female):

Body: Brass, Nickel Plated, Dielectric: PTFE

Center Contact: Beryllium Copper, Gold Plate

Banana Plug - Body: Brass, Nickel Plated

Spring: Beryllium Copper, Nickel Plated

Insulation - ABS Molded to BNC (Female) and Banana Plug Bodies, Color: Black

Marking: "1269 POMONA"

### RATINGS:

Operating Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 500 VRMS Max.

Operating Temperature: +50°C (+122°F) Max.

### ORDERING INFORMATION: Model 1269

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360  
Technical Assistance: 800-241-2060

PomonaACCESS 90497 (800) 444-6785 or (425) 446-6010  
More drawings available at [www.pomonaelectronics.com](http://www.pomonaelectronics.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[1269](#)