



FEATURES:

- Converts Standard Phone Jacks to Double Binding Posts.
- Banana Plugs can be stacked vertically or horizontally.
- Wires, spade lugs and pin tip plugs can be attached by means of the insulated knurl thumb knob.
- Insulated knurl thumb knob is captive to prevent misplacement.

MATERIALS:

Binding Post: Body – Brass, Nickel Plated

Insulator: Polycarbonate, Color: One black, one red

Insulator: ABS, molded to the binding post and phone plug

Marking: “ 1285 POMONA ELECTRONICS”

Phone Plug: Brass, Nickel Plated

RATINGS:

Operating Voltage: 500 VDC

Operating Temperature: +50°C (+122°F)

Current: 5 Amperes Max.

ORDERING INFORMATION: Model 1285

All dimensions are in inches. Tolerances (except noted): .xx = ±.02” (.51 mm), .xxx = ± .005” (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[1285](#)