



SCHEMATIC

### FEATURES:

- Right Angle BNC Provided for Easy Access
- Lengths other than those specified are available upon request.

### MATERIALS:

Conn: 1<sup>st</sup> End – Right Angle BNC Male.

Body and Fittings: Tarnish Resistant.

Center Contact: Gold Plated per MIL-C-39012.

Cable: RG58C/U. (.195) O.D.

50 Ohms Impedence

Marking: "POMONA 1383-C-XX".

Conn: 2<sup>nd</sup> End-BNC Male.

Body Fittings: Non-tarnish finish.

Center Contact: Gold Plated per MIL-C-39012.

### RATINGS: Entire Assembly

Operating Temperature: +50°C. (+122°F.) Max.

Operating Voltage: Shield-Earth: 30VAC/60VDC Max.

Inner conductor-Shield: 500 VRMS Max.

### ORDERING INFORMATION: Model 1383-C-XX

XX=Cable Length, Standard Lengths: 18" (457), 24" (610), 36" (914), 48" (1219), 60" (1524)

Ordering Example: 1383-C-60 indicates 60" (1524)

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[1383-C-60](#) [1383-C-24](#)