




**Model 1581, 2854 & 4900  
Panel Mount Banana Jack**



**Features**

- Banana Jacks mount into panels ranging in thickness from .063" (1.6mm) to .375" (9.5mm).
- Model 4900 features Polyphenylene Sulfide for high temperature applications.
- Model 2854 features gold plated body for optimum electrical connection.
- Model 1581 features bright tin plating.

**Materials**

Banana Jack: Body – Brass, Nickel Plated, (Model 2854, Brass, Gold Plated)  
 Insulators: Polycarbonate (Model 4900, High Temperature Polyphenylene Sulfide)  
 ¼ Internal Locking Washer: Steel, Nickel Plated  
 ¼-32 Hex Nut: Brass, Nickel Plated

**Ratings**

Operating Temperature: +115°C (+239°F), (Model 4900 +220°C (+428°F))  
 Operating Voltage: For *CE compliance* and for personal safety, do not hold in hand when voltages exceed 30 Vrms/60 Vdc.  
 Maximum voltage for *hands free use* in controlled testing environments: 2500 WVDC  
 Do not use on circuits where transient stresses can exceed the rated voltage.  
 Current: 15 Amperes

**Ordering Information** Model: #-Color Code

1581 Std. Colors: -0 Black, -1 Brown, -2 Red, -3 Orange, -4 Yellow, -5 Green, -6 Blue, -7 Violet, -8 Gray, -9 White  
 2854 Std. Colors: -0 Black, -1 Brown, -2 Red, -4 Yellow, -5 Green, -6 Blue, -8 Gray, -9 White (*Other colors available, contact Pomona Technical Support: [technicalsupport@pomonatest.com](mailto:technicalsupport@pomonatest.com)*)  
 4900 Std. Colors: -0 Black, -6 Blue  
 Sold unassembled, in packages of 10 per color  
 Ordering Example: 2854-2 Gold Plated Banana Jack, Color: Red

**USA:** Sales: 800-490-2361  
 Technical Support: [technicalsupport@pomonatest.com](mailto:technicalsupport@pomonatest.com)  
 Fax: 425-446-5844  
**Europe:** 31-(0) 40 2675 150 **International:** 425-446-5500  
**Where to Buy:** [www.pomonaelectronics.com](http://www.pomonaelectronics.com)

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Pomona:

[2854-8](#) [2854-4](#) [2854-1](#) [2854-0](#) [2854-6](#) [2854-9](#) [2854-5](#) [2854-2](#) [4900-0](#) [1581-02](#) [1581-6](#) [1581-8](#) [1581-4](#) [1581-9](#)  
[1581-1](#) [1581-3](#) [1581-7](#) [4900-6](#) [1581-0](#) [1581-2](#) [1581-5](#) [1581-3#/BULK](#) [1581-8#](#) [2854-0#](#) [1581-9#](#) [2854-5#](#)  
[1581-6#](#) [1581-5#](#) [1581-0#](#) [1581-2#](#)