



FEATURES:

- Permits pin tip cords to be used with equipment having banana jacks.

MATERIALS:

Upper Conn.: Pin Jack

Material: Spring – Beryllium Copper per QQ-C-533, Berylco 25, Cond. H.T.

Finish: Gold plated per MIL-G-45204, Type II, Class 00 over electroless nickel per MIL-C-26074, 200/300 microinches

Insulation: ABS molded to pin jack and banana plug body.

Marking: “1809” “POMONA ELECTRONICS CALIF.”

Lower Conn.: Standard Banana Plug

Material: Spring – Beryllium Copper per QQ-C-533, Berylco 25, Cond. HT.

Plug Body – Brass per QQ-B-626,

Alloy 360, ½ Hard

Finish: Nickel plated per QQ-N-290, Class 2, 200/300 micro-inches.

RATINGS:

Operating Voltage: 2500 WVDC

Operating Temperature: +50°C. (+122°F.) Max.

Current: 5 Amperes

ORDERING INFORMATION: Model 1809-*

*= Color, -0 Black, -2 Red

Ordering Example: 1809-2 Adapter Color is Red

Other colors available on special request.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

1809-2 1809-0