



### FEATURES:

- Provides a fast and easy method to splice two cables together to increase cable length.

### MATERIALS:

Jacks : Brass, Nickel Plated

Insulation: Polypropylene

### RATINGS:

Operating Voltage: 5000 VDC

Operating Temperature: +55° C. (+131° F.) Max.

Current: 15 Amperes Max.

### ORDERING INFORMATION: Model 1829-\*

\* = Color, Standard Colors: -0 Black, -2 Red

Sold in packages of ten.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

1829-0 1829-2